



Model (Metric)	Thread		Dimensions [in. (mm)]					
	A	B	C	D	E	F	G	H
MRL-1.5	8-32 (M4)	1/4-20 (M6)					0.75 (18.7)	1.50 (37.5)
MRL-3	8-32 (M4)	1/4-20 (M6)	1.000 (25.0)			1.000 (25.0)		3.00 (75.0)
MRL-6M	8-32 (M4)	1/4-20 (M6)	1.000 (25.0)			1.000 (25.0)		6.00 (150.0)
MRL-12M	8-32 (M4)	1/4-20 (M6)	1.000 (25.0)	0.810 (20.6)	0.595 (14.7)	1.000 (25.0)		12.00 (300.0)
MRL-18M	8-32 (M4)	1/4-20 (M6)	1.000 (25.0)	0.810 (20.6)	0.595 (14.7)	1.000 (25.0)		18.00 (450.0)
MRL-24M	8-32 (M4)	1/4-20 (M6)	1.000 (25.0)	0.810 (20.6)	0.595 (14.7)	1.000 (25.0)		24.00 (600.0)

MRL-18M-ART-S (1281749)