



- Interface with: M-UMR5 and M-MVN50
4 holes M3 clr / □ 20
- Interface: M-UTR46 with M-BR3
4 holes M3 thd / □ 36
- Interface with: M-UTR46 and M-PO46
4 holes M3 clr / Ø 38
- 2 holes M4 clr, 40 spacing
- Interface with: M-UTM
4 holes M4 clr / □ 63
- 8 holes M4 clr □ 46 x 76.2
- Interface with: M-UTR80 and M-PO80
4 holes M4 clr / Ø 68 (or □ 48)
- 4 holes M4 thd / □ 77
- 2 holes M5 clr, 40 spacing
- Interface with: Rod and Optics table
1 hole M6 clr