



- Interface with: M-UMR5 and M-MVN50
4 holes M3 clr / □ 20
- Interface with: M-UMR3.5
2 holes M3 clr, 20 spacing
- Interface with: M-UMR3.5
2 holes M3 thd, 20 spacing
- Interface: M-UTR46 with M-BR3
4 holes M3 thd / □ 36
- Interface with: M-UTR46 and M-P046
4 holes M3 thd / Ø 38
- 4 holes M3 thd / □ 43
- Interface with: Rod and Optics table
1 hole M6 clr