



Model (Metric)	Dimensions [in. (mm)]						Thread	
	A	B	C	D	E	F	V	W
BR3	0.31 (8)	0.26 (6.5)	0.08 (2)	0.09 (2.2)	0.02 (0.5)	0.20 (5)	0.39 (10)	4-40 (M3) 0.13 (3.3)
BR32	0.31 (8)	0.18 (4.5)	0.08 (2)	0.09 (2.2)	0.02 (0.5)	0.12 (3)	0.31 (8)	4-40 (M3) 0.13 (3.3)
BR4	0.51 (13)	0.30 (7.5)	0.10 (2.5)	0.18 (4.5)	0.02 (0.5)	0.24 (6)	0.47 (12)	8-32 (M4) 0.17 (4.4)
M-BR41 ¹	0.51 (13)	0.18 (4.5)	0.08 (2)	0.18 (4.5)	0.02 (0.5)	0.12 (3)	0.39 (10)	M4 M4
BR42	0.51 (13)	0.22 (5.5)	0.08 (2)	0.18 (4.5)	0.02 (0.5)	0.12 (3)	0.39 (10)	8-32 (M4) 0.17 (4.4)
BR5	0.59 (15)	0.41 (10.5)	0.12 (3)	0.18 (4.5)	0.04 (1)	0.31 (8)	0.63 (16)	10-24 (M5) 0.22 (5.5)
BR6	1.02 (26)	0.49 (12.5)	0.35 (9)	0.39 (10)	0.04 (1)	0.39 (10)	0.79 (20)	1/4-20 (M6) 0.26 (6.6)
BR62	0.94 (24)	0.33 (8.5)	0.12 (3)	0.37 (9.5)	0.04 (1)	0.24 (6)	0.63 (16)	1/4-20 (M6) 0.28 (7)
BR68 ²	1.26 (32)	0.33 (8.5)	0.20 (5)		0.04 (1)	0.24 (6)	0.47 (12)	1/4-20 (M6)

¹ M-BR41 Bridles use CHCTB M4 X 10mm captive screws model M-CAP-M42.

² Only M-BR68 available.