



Model	A	B	C
9942	0.375 (9.5)	2-56	8-32
9942-M	0.375 (9.5)	M2	M4
9943	0.50 (12.7)	8-32	8-32
9943-M	0.50 (12.7)	M4	M4
9944	1.00 (25.4)	8-32	8-32
9944-M	1.00 (25.4)	M4	M4
9945	1.50 (38.1)	8-32	8-32
9945-M	1.50 (38.1)	M4	M4
9946	2.00 (50.8)	8-32	8-32
9946-M	2.00 (50.8)	M4	M4