



- Interface with: M-UMR5 and M-MVN50
 4 holes M3 clr / □ 20
- Interface with: M-UMR8 and M-MVN80
 4 holes M4 clr / □ 34
- 2 holes M4 clr, 40 spacing
- 2 holes M4 clr, 63 spacing
- Interface: M-UTR80 with M-BR4
 4 holes M4 thd / □ 63
- Interface with: M-UTR80 and M-PO80
 4 holes M4 clr / Ø 68 (or □ 48)
- 4 holes M4 thd / □ 77
- 2 holes M5 clr, 40 spacing
- Interface with: Rod and Optics table
 1 hole M6 clr