

4 holes M3 thd / h 43



Interface with: AX48 and T50  
4 holes M4 clr / h 20



Interface with: AX48 and T50  
2 holes M4 clr, 20 spacing



Interface with: M-UMR8 and M-MVN80  
4 holes M4 clr / h 34

