



Dimensions [in. (mm)]

Model	A	B	F	H
B6.35	0.25 (6.35)	0.05–0.14 (1.2–3.5)	0.20 (5)	0.24 (6)
B12.7	0.50 (12.7)	0.05–0.20 (1.2–5)	0.43 (11)	0.31 (8)