



M-SG-30x30-4	750 mm	750 mm	M6
M-SG-30x36-4	750 mm	900 mm	M6
M-SG-30x48-4	750 mm	1200 mm	M6
M-SG-30x60-4	750 mm	1500 mm	M6
M-SG-33-4	900 mm	900 mm	M6
M-SG-34-4	900 mm	1200 mm	M6
M-SG-35-4	900 mm	1500 mm	M6
M-SG-36-4	900 mm	1800 mm	M6
M-SG-44-4	1200 mm	1200 mm	M6
M-SG-45-4	1200 mm	1500 mm	M6
M-SG-46-4	1200 mm	1800 mm	M6
M-SG-48-4	1200 mm	2400 mm	M6
SG-11-4	1 ft.	1 ft.	1/4-20
SG-12-4	1 ft.	2 ft.	1/4-20
SG-13-4	1 ft.	3 ft.	1/4-20
SG-14-4	1 ft.	4 ft.	1/4-20
SG-22-4	2 ft.	2 ft.	1/4-20
SG-23-4	2 ft.	3 ft.	1/4-20
SG-24-4	2 ft.	4 ft.	1/4-20
SG-25-4	2 ft.	5 ft.	1/4-20
SG-26-4	2 ft.	6 ft.	1/4-20
SG-30x30-4	30 in.	30 in.	1/4-20
SG-30x36-4	30 in.	36 in.	1/4-20
SG-30x48-4	30 in.	48 in.	1/4-20
SG-30x60-2	30 in.	60 in.	1/4-20
SG-33-4	3 ft.	3 ft.	1/4-20
SG-34-4	3 ft.	4 ft.	1/4-20
SG-35-4	3 ft.	5 ft.	1/4-20
SG-36-4	3 ft.	6 ft.	1/4-20
SG-44-4	4 ft.	4 ft.	1/4-20
SG-45-4	4 ft.	5 ft.	1/4-20
SG-46-4	4 ft.	6 ft.	1/4-20
SG-48-4	4 ft.	8 ft.	1/4-20



Model (-ML version have the same values)	A	B	Mounting Holes
LC-25-4	2 ft.	5 ft.	1/4-20
LC-35-4	3 ft.	5 ft.	1/4-20
M-LC-25-4	600 mm	1500 mm	M6
M-LC-25-4	900 mm	1500 mm	M6
M-SG-11-4	300 mm	300 mm	M6
M-SG-12-4	300 mm	600 mm	M6
M-SG-13-4	300 mm	900 mm	M6
M-SG-14-4	300 mm	1200 m	M6
M-SG-22-4	600 mm	600 mm	M6
M-SG-23-4	600 mm	900 mm	M6
M-SG-24-4	600 mm	1200 mm	M6
M-SG-25-4	600 mm	1500 mm	M6
M-SG-26-4	600 mm	1800 mm	M6