



Model	A	B	C
AJS100-05H-NL	1.29 in. (32.8 mm)	0.50 in. (12.7 mm)	1/4-100
AJS170-05H-NL	1.41 in. (35.8 mm)	0.50 in. (12.7 mm)	1/4-170
AJS170-05H-NL-V6	1.41 in. (35.8 mm)	0.50 in. (12.7 mm)	1/4-170
AJS254-05H-NL	1.29 in. (32.7 mm)	0.50 in. (12.7 mm)	1/4-254