



Model (Metric)	Thread		Dimensions [in. (mm)]							
	A	B	C	ϕD	E	F	ϕG	H	J	K
UTR46	8-32 (M4)	1/4-20 (M6)	1.000 (25.0)	0.291 (7.4)	1.00 (25.4)	2.98 (75.8)	1.81 (46)	1.97 (50)	3.50 (89)	1.30 (33)
UTR46S	8-32 (M4)	1/4-20 (M6)	1.000 (25.0)	0.291 (7.4)	1.00 (25.4)	2.98 (75.8)	1.81 (46)	1.97 (50)	3.50 (89)	0.91 (23)
UTR80	8-32 (M4)	1/4-20 (M6)	2.000 (50.0)	0.295 (7.5)	1.98 (50.4)	3.98 (101.1)	3.11 (79)	3.15 (80)	4.72 (120)	1.57 (40)
UTR80S	8-32 (M4)	1/4-20 (M6)	2.000 (50.0)	0.295 (7.5)	1.98 (50.4)	3.98 (101.1)	3.11 (79)	3.15 (80)	4.72 (120)	0.91 (23)