



Model	Dim "A"
OC1-LH1	1.035-40 Thd. Thru
OC1-RMS	0.800-36 Thd. Thru
OC1-DM	1.505 in. (38.2 mm) Thru
OC1-BT	1.26 in (32.0 mm) Thru