



Model	THD A	B	C	D
M-PS-A	M6	31.8 mm	11.2 mm	4.8 mm
M-PS-AZ	M6	31.8mm	11.2 mm	4.8 mm
PS-A	1/4-20	1.25 in.	0.44 in.	0.19 in.
PS-AZ	1/4-20	1.25 in.	0.44 in.	0.19 in.