



ø.375 (9.522) MAX.  
ø.374 (9.499) MIN.

**MODEL SHOWN: CONEX-TRB12CC**  
DIMENSIONS IN INCHES (AND MILLIMETERS)  
0 5 10 20 30 IN. (MM)  
SCALE 3:4

