



Model	Dimensions [in. (mm)]		Thread
	A	B	C
AJS100-05K	1.41 in. (35.8 mm)	0.50 in. (12.7 mm)	1/4-100
AJS127-0.5K	1.41 in. (35.8 mm)	0.50 in. (12.7 mm)	1/4-127