



Model	A	B	C	D	E	G	H	Note
U100-A	2.0 in.	na,	1.14 in.	0.63 in.	1.0 in.	0.31 in.	8-32	Actuators sold separately
U100-A2H	2.0 in.	1.79 in.	1.14 in.	0.63 in.	1.0 in.	0.31 in.	8-32	No knobs on adjusters
U100-A2K	2.0 in.	1.79 in.	1.14 in.	0.63 in.	1.0 in.	0.31 in.	8-32	
U100-A2K-170N	2.0 in.	1.79 in.	1.14 in.	0.63 in.	1.0 in.	0.31 in.	8-32	
U100-A2K-PK	2.0 in.	1.79 in.	1.14 in.	0.63 in.	1.0 in.	0.31 in.	8-32	
U100-A-30	2.0 in.	na	1.14 in.	0.63 in.	1.0 in.	0.31 in.	8-32	Actuators sold separately
U100-A3H	2.0 in.	1.79 in.	1.14 in.	0.63 in.	1.0 in.	0.31 in.	8-32	No knobs on adjusters
U100-A3K	2.0 in.	1.79 in.	1.14 in.	0.63 in.	1.0 in.	0.31 in.	8-32	
U100-A3K-170N	2.0 in.	1.79 in.	1.14 in.	0.63 in.	1.0 in.	0.31 in.	8-32	
U100-A-LH	2.0 in.	na	1.14 in.	0.63 in.	1.0 in.	0.31 in.	8-32	Mirror Image of Drawing Shown, Actuators sold separately
U100-A-LH-2H	2.0 in.	1.79 in.	1.14 in.	0.63 in.	1.0 in.	0.31 in.	8-32 (M4)	Mirror Image of Drawing Shown, No knobs on adjusters
U100-A-LH-2K	2.0 in.	1.79 in.	1.14 in.	0.63 in.	1.0 in.	0.31 in.	8-32 (M4)	Mirror Image of Drawing Shown
U100-A-LH-3H	2.0 in.	1.79 in.	1.14 in.	0.63 in.	1.0 in.	0.31 in.	8-32 (M4)	Mirror Image of Drawing Shown, No knobs on adjusters
U100-A-LH-3K	2.0 in.	1.79 in.	1.14 in.	0.63 in.	1.0 in.	0.31 in.	8-32 (M4)	Mirror Image of Drawing Shown
U200-A	2.75 in.	na	1.31 in.	0.63 in.	1.38 in.	0.31 in.	8-32	Actuators sold separately
U200-A-LH	2.75 in.	na	1.31 in.	0.63 in.	1.38 in.	0.31 in.	8-32	Mirror Image of Drawing Shown, Actuators sold separately
U200-A2H	2.75 in.	1.95 in.	1.31 in.	0.63 in.	1.38 in.	0.31 in.	8-32	No knobs on adjusters
U200-A2K	2.75 in.	1.95 in.	1.31 in.	0.63 in.	1.38 in.	0.31 in.	8-32	
U200-A3H	2.75 in.	1.95 in.	1.31 in.	0.63 in.	1.38 in.	0.31 in.	8-32	No knobs on adjusters
U200-A3K	2.75 in.	1.95 in.	1.31 in.	0.63 in.	1.38 in.	0.31 in.	8-32	
U300-A	3.75 in.	na	1.31 in.	0.63 in.	1.88 in.	0.31 in.	8-32	Actuators sold separately
U300-A2K	3.75 in.	1.95 in.	1.31 in.	0.63 in.	1.88 in.	0.31 in.	8-32	* U300-A mounts have 3 clearance holes with 0.50 in. (12.7 mm) spacing
U300-A3K	3.75 in.	1.95 in.	1.31 in.	0.63 in.	1.88 in.	0.31 in.	8-32	* U300-A mounts have 3 clearance holes with 0.50 in. (12.7 mm) spacing