



Model	Dimensions [in. (mm)]		Thread
	A	B	
AJS127-0.5	1.41 (35.8)	0.50 (12.7)	1/4-127
AJS100-0.5	1.41 (35.8)	0.50 (12.7)	1/4-100
AJS100-1	2.10 (53.3)	1.00 (25.4)	1/4-100
AJS100-2	2.97 (75.4)	2.00 (50.8)	1/4-100
AJS20-0.5	1.41 (35.8)	0.50 (12.7)	1/4-20
AJS20-1	2.10 (53.3)	1.00 (25.4)	1/4-20
AJS20-2	2.97 (75.4)	2.00 (50.8)	1/4-20