



Model	A	B	Mounting Holes
(-ML version have the same values)			
M-SG-11-2	300 mm	300 mm	M6
M-SG-12-2	300 mm	600 mm	M6
M-SG-13-2	300 mm	900 mm	M6
M-SG-14-2	300 mm	1200 mm	M6
M-SG-22-2	600 mm	600 mm	M6
M-SG-23-2	600 mm	900 mm	M6
M-SG-24-2	600 mm	1200 mm	M6
M-SG-25-2	600 mm	1500 mm	M6
M-SG-26-2	600 mm	1800 mm	M6
M-SG-30x30-2	750 mm	750 mm	M6
M-SG-30x36-2	750 mm	900 mm	M6
M-SG-30x48-2	750 mm	1200 mm	M6
M-SG-30x60-2	750 mm	1500 mm	M6
M-SG-33-2	900 mm	900 mm	M6
M-SG-34-2	900 mm	1200 mm	M6
M-SG-35-2	900 mm	1500 mm	M6
M-SG-36-2	900 mm	1800 mm	M6
M-SG-44-2	1200 mm	1200 mm	M6
M-SG-45-2	1200 mm	1500 mm	M6
M-SG-46-2	1200 mm	1800 mm	M6
M-SG-48-2	1200 mm	2400 mm	M6
SG-11-2	1 ft.	1 ft.	1/4-20
SG-12-2	1 ft.	2 ft.	1/4-20
SG-13-2	1 ft.	3 ft.	1/4-20
SG-14-2:	1 ft.	4 ft.	1/4-20
SG-22-2	2 ft.	2 ft.	1/4-20
SG-23-2	2 ft.	3 ft.	1/4-20
SG-24-2	2 ft.	4 ft.	1/4-20
SG-25-2	2 ft.	5 ft.	1/4-20
SG-26-2	2 ft.	6 ft.	1/4-20
SG-30x30-2	30 in.	30 in.	1/4-20
SG-30x36-2	30 in.	36 in.	1/4-20
SG-30x48-2	30 in.	48 in.	1/4-20
SG-30x60-2	30 in.	60 in.	1/4-20
SG-33-2	3 ft.	3 ft.	1/4-20
SG-34-2	3 ft.	4 ft.	1/4-20
SG-35-2	3 ft.	5 ft.	1/4-20
SG-36-2	3 ft.	6 ft.	1/4-20
SG-44-2	4 ft.	4 ft.	1/4-20
SG-45-2	4 ft.	5 ft.	1/4-20
SG-46-2	4 ft.	6 ft.	1/4-20
SG-48-2	4 ft.	8 ft.	1/4-20

