



	A	B	C	D
M-EN40:	40 mm	25 to 67 mm	102 mm	16 mm
M-EN60:	60 mm	45 to 115 mm	156 mm	25 mm
M-EN86:	86 mm	65 to 170 mm	222 mm	30 mm.

Threaded Holes (on top and bottom of stage):

M6 center, M3 on 20x20 mm pattern, M3 on 36x36 mm pattern, M3 on 53x53 mm pattern,
M4 on 63x63 mm pattern, M4 on 77x77 mm pattern