



Model	A	B
Q-CC-1	0.50 in. (12.7 mm)	0.35 in. (8.9 mm)
Q-RG-10	8.0 in. (203 mm)	0.80 in. (20.3 mm)
Q-RG-12	10.0 in. (254 mm)	0.80 in. (20.3 mm)
Q-RG-4	2.0 in. (50.8 mm)	0.80 in. (20.3 mm)
Q-RG-6	4.0 in. (101.6 mm)	0.80 in. (20.3 mm)
Q-RG-8	6.0 in. (154.4 mm)	0.80 in. (20.3 mm)