



Model	A	B	Mounting Holes
M-PG-12-4	300 mm	600 mm	M6
M-PG-13-4	300 mm	900 mm	M6
M-PG-14-4	300 mm	1200 mm	M6
M-PG-22-4	600 mm	600 mm	M6
M-PG-23-4	600 mm	900 mm	M6
M-PG-24-4	600 mm	1200 mm	M6
M-PG-25-4	600 mm	1500 mm	M6
M-PG-26-4	600 mm	1800 mm	M6
M-PG-30x30-4	750 mm	750 mm	M6
M-PG-30x36-4	750 mm	900 mm	M6
M-PG-30x48-4	750 mm	1200 mm	M6
M-PG-33-4	900 mm	900 mm	M6
M-PG-34-4	900 mm	1200 mm	M6
M-PG-35-4	900 mm	1500 mm	M6
M-PG-36-4	900 mm	1800 mm	M6
PG-12-4	1 ft.	2 ft.	1/4-20
PG-13-4	1 ft.	3 ft.	1/4-20
PG-14-4	1 ft.	4 ft.	1/4-20
PG-22-4	2 ft.	2 ft.	1/4-20
PG-23-4	2 ft.	3 ft.	1/4-20
PG-24-4	2 ft.	4 ft.	1/4-20
PG-25-4	2 ft.	5 ft.	1/4-20
PG-26-4	2 ft.	6 ft.	1/4-20
PG-30x30-4	30 in.	30 in.	1/4-20
PG-30x36-4	30 in.	36 in.	1/4-20
PG-30x48-4	30 in.	48 in.	1/4-20
PG-33-4	3 ft.	3 ft.	1/4-20
PG-34-4	3 ft.	4 ft.	1/4-20
PG-35-4	3 ft.	5 ft.	1/4-20
PG-36-4	3 ft.	6 ft.	1/4-20

