



Model	A	B	C	D
MFM-075	0.71 in. C'Bore 0.75 in.	1.28 in.	0.14 in.	0.64 in.
MFM-075-HR	0.71 in. C'Bore 0.75 in.	1.28 in.	0.14 in.	0.64 in.
MFM-075-LC	0.71 in. C'Bore 0.75 in.	1.28 in.	0.14 in.	0.64 in.
MFM-100	0.96 in. C'Bore 1.01 in.	1.50 in.	0.25 in.	0.75 in.
MFM-100-HR	0.96 in. C'Bore 1.01 in.	1.50 in.	0.25 in.	0.75 in.
MFM-100-LC	0.96 in. C'Bore 1.01 in.	1.50 in.	0.25 in.	0.75 in.