


1.08 (27.4)



Model (Metric)	Width (A)	Length (B)	
		[in. (mm)]	[in. (mm)]
TD-11 (M-TD-11 )	12 (300)	12 (300)	12 (300)
TD-12 (M-TD-12 )	12 (300)	24 (600)	24 (600)
TD-13 (M-TD-13 )	12 (300)	36 (900)	36 (900)
TD-22 (M-TD-22 )	24 (600)	24 (600)	24 (600)
TD-23 (M-TD-23 )	24 (600)	36 (900)	36 (900)