



Model	A	B	C	D	E	F	G	H
481-A	8-32	1/4-20	0.50 in.	1.00 in.	1.984 in.	2.953 in.	0.125 in.	0.44 in.
M-481-A	M4	M6	12.5 mm	25 mm	50 mm	75 mm	3.8 mm	11.6 mm