

Model	Diameter (mm)	Thickness (mm)
SAW11	5.00	1.00
SAW12	6.35	0.50
SAW13	9.50	0.50
SAW14	10.00	1.00
SAW15	12.70	3.18
SAW17	13.00	0.50
SAW18	15.00	2.00
SAW19	17.25	2.00
SAW21	22.00	1.00
SAW22	23.75	1.00
SAW23	25.00	2.30
SAW24	25.40	2.30
SAW25	30.00	1.00
SAW26	31.75	1.00
SAW27	35.00	1.00
SAW28	38.10	1.00
SAW29	40.00	2.00
SAW31	50.80	3.15
SAW32	75.00	2.00

