



Model	A	B
HX1.5M	1.5 mm	0.5" [12.7 mm]
HX2.5M	2.5 mm	0.5" [12.7 mm]
HX3M	3.0 mm	0.5" [12.7 mm]
HX5M	5.0 mm	0.8" [20.3 mm]
HX.050-1.27M	.050" [1.27 mm]	0.5" [12.7 mm]
HX.078-2M	5/64" [2.0 mm]	0.5" [12.7 mm]
HX.156-4M	5/32" [4.0 mm]	0.8" [20.3 mm]
HX.125	1/8"	0.8" [20.3 mm]
HX.141	9/64"	0.8" [20.3 mm]
HX.188	3/16"	0.8" [20.3 mm]