



- TECH SPECS:
1. X / Y TRANSLATION: $\pm 1.6\text{mm}$ AT $254\mu\text{m/rev}$; $0.71\mu\text{m}$ SENSITIVITY
 2. Z-TRAVEL: $\pm 1.6\text{mm}$, AT $1.41\mu\text{m}$ SENSITIVITY
 3. CLEAR APERTURE: $\phi .90 [22.9\text{mm}]$
 4. OPTICS AXIS HEIGHT: $1.0 [25.4\text{mm}]$
 5. MAX OPTICS EDGE THICKNESS: $0.46 [11.7\text{mm}]$

MODEL	D in (mm)	MOUNTING HOLE THREAD
LPXYZ-1H	0.50 (12.7)	8-32
M-LPXYZ-1H	0.47 (12.0)	M4 x 0.7

MODEL: LPXYZ-1H & M-LPXYZ-1H

