

MODEL NUMBER	DIM A (in [mm])	DIM B (in [mm])	DIM C (in)	DIM D (in)
SGD-22-2	24.0	24.0	2.00	2.32
SGD-23-2	24.0	36.0	2.00	2.32
SGD-24-2	24.0	48.0	2.00	2.32
SGD-35-2	36.0	60.0	2.00	2.32
SGD-36-2	36.0	72.0	2.00	2.32
SGD-23-4	24.0	36.0	4.00	4.32
SGD-24-4	24.0	48.0	4.00	4.32
SGD-35-4	36.0	60.0	4.00	4.32
SGD-36-4	36.0 in	72.0	4.00	4.32
M-SGD-22-2	23.62 [600]	23.62 [600]	2.00	2.32
M-SGD-23-2	23.62 [600]	35.43 [900]	2.00	2.32
M-SGD-24-2	23.62 [600]	47.24 [1200]	2.00	2.32
M-SGD-35-2	35.43 [900]	59.06 [1500]	2.00	2.32
M-SGD-36-2	35.43 [900]	70.85 [1800]	2.00	2.32
M-SGD-23-4	23.62 [600]	35.43 [900]	4.00	4.32
M-SGD-24-4	23.62 [600]	47.24 [1200]	4.00	4.32
M-SGD-35-4	35.43 [900]	59.06 [1500]	4.00	4.32
M-SGD-36-4	35.43 [900]	70.85 [1800]	4.00	4.32

