



Model	W	L	T	Mounting Holes	# of Microlocks
IG-11-2-ML	1 ft.	1 ft.	2.3 in.	1/4-20	4
IG-12-2-ML	1 ft.	2 ft.	2.3 in.	1/4-20	4
IG-13-2-ML	1 ft.	3 ft.	2.3 in.	1/4-20	4
IG-14-2-ML	1 ft.	4 ft.	2.3 in.	1/4-20	5
IG-22-2-ML	2 ft.	2 ft.	2.3 in.	1/4-20	5
IG-23-2-ML	2 ft.	3 ft.	2.3 in.	1/4-20	5
IG-24-2-ML	2 ft.	4 ft.	2.3 in.	1/4-20	5
IG-25-2-ML	2 ft.	5 ft.	2.3 in.	1/4-20	5
IG-26-2-ML	2 ft.	6 ft.	2.3 in.	1/4-20	5
IG-33-2-ML	3 ft.	3 ft.	2.3 in.	1/4-20	5
IG-34-2-ML	3 ft.	4 ft.	2.3 in.	1/4-20	5
IG-35-2-ML	3 ft.	5 ft.	2.3 in.	1/4-20	5
IG-36-2-ML	3 ft.	6 ft.	2.3 in.	1/4-20	5
IG-44-2-ML	4 ft.	4 ft.	2.3 in.	1/4-20	5
IG-45-2-ML	4 ft.	5 ft.	2.3 in.	1/4-20	5
IG-46-2-ML	4 ft.	6 ft.	2.3 in.	1/4-20	5
IG-48-2-ML	4 ft.	8 ft.	2.3 in.	1/4-20	5
M-IG-11-2-ML	300 mm	300 mm	58 mm	M6	4
M-IG-12-2-ML	300 mm	600 mm	58 mm	M6	4
M-IG-13-2-ML	300 mm	900 mm	58 mm	M6	4
M-IG-14-2-ML	300 mm	1200 mm	58 mm	M6	5
M-IG-22-2-ML	600 mm	600 mm	58 mm	M6	5
M-IG-23-2-ML	600 mm	900 mm	58 mm	M6	5
M-IG-24-2-ML	600 mm	1200 mm	58 mm	M6	5
M-IG-25-2-ML	600 mm	1500 mm	58 mm	M6	5
M-IG-26-2-ML	600 mm	1800 mm	58 mm	M6	5
M-IG-33-2-ML	900 mm	900 mm	58 mm	M6	5
M-IG-34-2-ML	900 mm	1200 mm	58 mm	M6	5
M-IG-35-2-ML	900 mm	1500 mm	58 mm	M6	5
M-IG-36-2-ML	900 mm	1800 mm	58 mm	M6	5
M-IG-44-2-ML	1200 mm	1200 mm	58 mm	M6	5
M-IG-45-2-ML	1200 mm	1500 mm	58 mm	M6	5
M-IG-46-2-ML	1200 mm	1800 mm	58 mm	M6	5
M-IG-48-2-ML	1200 mm	2400 mm	58 mm	M6	5