

MODEL NUMBER	A in. [mm]	B in. [mm]	C in. [mm]	D in. [mm]	E in. [mm]	F in	G mm
M-INT3-36-8-N	35.4 [900]	70.9 [1800]	8 [203]	31.6 [803]	67.6 [1717]	36.7	932
M-INT3-36-12-N	35.4 [900]	70.9 [1800]	12 [305]	31.6 [803]	67.6 [1717]	40.7	1034
M-INT3-38-8-N	35.4 [900]	94.5 [2400]	8 [203]	31.6 [803]	91.6 [2327]	36.7	932
M-INT3-38-12-N	35.4 [900]	94.5 [2400]	12 [305]	31.6 [803]	91.6 [2327]	40.7	1034
M-INT3-46-8-N	47.2 [1200]	70.9 [1800]	8 [203]	43.6 [1107]	67.6 [1717]	36.7	932
M-INT3-46-12-N	47.2 [1200]	70.9 [1800]	12 [305]	43.6 [1107]	67.6 [1717]	40.7	1034
M-INT3-47-8-N	47.2 [1200]	82.7 [2100]	8 [203]	43.6 [1107]	79.6 [2022]	36.7	932
M-INT3-47-12-N	47.2 [1200]	82.7 [2100]	12 [305]	43.6 [1107]	79.6 [2022]	40.7	1034
M-INT3-48-8-N	47.2 [1200]	94.5 [2400]	8 [203]	43.6 [1107]	91.6 [2327]	36.7	932
M-INT3-48-12-N	47.2 [1200]	94.5 [2400]	12 [305]	43.6 [1107]	91.6 [2327]	40.7	1034
M-INT3-49-8-N	47.2 [1200]	106.3 [2700]	8 [203]	43.6 [1107]	103.6 [2631]	36.7	932
M-INT3-49-12-N	47.2 [1200]	106.3 [2700]	12 [305]	43.6 [1107]	103.6 [2631]	40.7	1034
M-INT3-410-8-N	47.2 [1200]	118.1 [3000]	8 [203]	43.6 [1107]	115.6 [2936]	36.7	932
M-INT3-410-12-N	47.2 [1200]	118.1 [3000]	12 [305]	43.6 [1107]	115.6 [2936]	40.7	1034
M-INT3-56-8-N	59.06 [1500]	70.9 [1800]	8 [203]	55.6 [1412]	67.6 [1717]	36.7	932
M-INT3-56-12-N	59.06 [1500]	70.9 [1800]	12 [305]	55.6 [1412]	67.6 [1717]	40.7	1034
M-INT3-57-8-N	59.06 [1500]	82.7 [2100]	8 [203]	55.6 [1412]	79.6 [2022]	36.7	932
M-INT3-57-12-N	59.06 [1500]	82.7 [2100]	12 [305]	55.6 [1412]	79.6 [2022]	40.7	1034
M-INT3-58-8-N	59.06 [1500]	94.5 [2400]	8 [203]	55.6 [1412]	91.6 [2327]	36.7	932
M-INT3-58-12-N	59.06 [1500]	94.5 [2400]	12 [305]	55.6 [1412]	91.6 [2327]	40.7	1034
M-INT3-59-8-N	59.06 [1500]	106.3 [2700]	8 [203]	55.6 [1412]	103.6 [2631]	36.7	932
M-INT3-59-12-N	59.06 [1500]	106.3 [2700]	12 [305]	55.6 [1412]	103.6 [2631]	40.7	1034
M-INT3-510-8-N	59.06 [1500]	118.1 [3000]	8 [203]	55.6 [1412]	115.6 [2936]	36.7	932
M-INT3-510-12-N	59.06 [1500]	118.1 [3000]	12 [305]	55.6 [1412]	115.6 [2936]	40.7	1034

NOTES:

1. M-INT3 OPTICAL TABLE HAS 4.8mm SKIN AND ONE PRECISION TUNABLE DAMPER
2. DIMS IN [] ARE IN mm.

