



| MODEL NO. | LENGTH |
|-----------|---------|
| OC1-GR-1 | 1.0 in |
| OC1-GR-2 | 2.0 in |
| OC1-GR-3 | 3.0 in |
| OC1-GR-4 | 4.0 in |
| OC1-GR-6 | 6.0 in |
| OC1-GR-8 | 8.0 in |
| OC1-GR-10 | 10.0 in |
| OC1-GR-12 | 12.0 in |
| OC1-GR-18 | 18.0 in |
| OC1-GR-24 | 24.0 in |