



Model	A	B	Mounting Holes
M-PG-12-2	300 mm	600 mm	M6
M-PG-13-2	300 mm	900 mm	M6
M-PG-14-2	300 mm	1200 mm	M6
M-PG-22-2	600 mm	600 mm	M6
M-PG-23-2	600 mm	900 mm	M6
M-PG-24-2	600 mm	1200 mm	M6
M-PG-25-2	600 mm	1500 mm	M6
M-PG-26-2	600 mm	1800 mm	M6
M-PG-30x30-2	750 mm	750 mm	M6
M-PG-30x36-2	750 mm	900 mm	M6
M-PG-30x48-2	750 mm	1200 mm	M6
M-PG-33-2	900 mm	900 mm	M6
M-PG-34-2	900 mm	1200 mm	M6
M-PG-35-2	900 mm	1500 mm	M6
M-PG-36-2	900 mm	1800 mm	M6
PG-12-2	1 ft.	2 ft.	1/4-20
PG-13-2	1 ft.	3 ft.	1/4-20
PG-14-2:	1 ft.	4 ft.	1/4-20
PG-22-2	2 ft.	2 ft.	1/4-20
PG-23-2	2 ft.	3 ft.	1/4-20
PG-24-2	2 ft.	4 ft.	1/4-20
PG-25-2	2 ft.	5 ft.	1/4-20
PG-26-2	2 ft.	6 ft.	1/4-20
PG-30x30-2	30 in.	30 in.	1/4-20
PG-30x36-2	30 in.	36 in.	1/4-20
PG-30x48-2	30 in.	48 in.	1/4-20
PG-33-2	3 ft.	3 ft.	1/4-20
PG-34-2	3 ft.	4 ft.	1/4-20
PG-35-2	3 ft.	5 ft.	1/4-20
PG-36-2	3 ft.	6 ft.	1/4-20

2.32 (58.9)

