



PART NUMBER	W (in)	L (in)	QTY OF ISOLATORS	ISOLATOR	MIN. LOAD lbs (kg)	MAX. LOAD lbs (kg)
VIP320-1218-1035	12	18	4	VIB320-0812	10 (4.5)	30 (15.9)
VIP320-1218-1555	12	18	3	VIB320-2340	15 (6.8)	55 (24.9)
VIP320-1218-5590	12	18	4	VIB320-1630	55 (24.9)	90 (40.8)
VIP320-1218-75125	12	18	4	VIB320-2340	75 (34.0)	125 (56.7)
VIP320-1218-135210	12	18	4	VIB320-3658	135 (61.2)	210 (95.3)
VIP320-1824-3070	18	24	4	VIB320-1630	30 (13.6)	70 (31.8)
VIP320-1824-50105	18	24	4	VIB320-2340	50 (22.7)	105 (47.6)
VIP320-1824-70140	18	24	4	VIB320-2947	70 (31.8)	140 (63.5)
VIP320-1824-95180	18	24	4	VIB320-3658	95 (43.1)	180 (81.6)
VIP320-1824-150350	18	24	4	VIB320-50100	150 (68)	350 (158.8)
VIP320-2430-2075	24	30	4	VIB320-2340	20 (9.1)	75 (34)
VIP320-2430-40110	24	30	4	VIB320-2947	40 (18.1)	110 (49.9)
VIP320-2430-65120	24	30	4	VIB320-3658	65 (29.5)	120 (54.4)
VIP320-2430-70125	24	30	4	VIB320-3658	70 (31.8)	125 (56.7)
VIP320-2430-75140	24	30	4	VIB320-3658	75 (34)	140 (63.5)
VIP320-2430-80200	24	30	4	VIB320-3775	80 (36.3)	200 (90.7)
VIP320-2430-120260	24	30	4	VIB320-5085	120 (54.4)	260 (117.9)
VIP320-2430-140320	24	30	4	VIB320-50100	140 (63.5)	320 (145.1)
VIP320-2430-275400	24	30	4	VIB320-85130	275 (124.7)	400 (181.4)
VIP320-2430-340520	24	30	4	VIB320-92150	340 (154.2)	520 (235.9)
VIP320-2638-100300	26	38	4	VIB320-3775	100 (45.4)	300 (136.1)