



[19.8]  
.78

[16]  
.63 GAP



PART NUMBER	A in. [mm]	B in. [mm]
VIS-LS-SS-3030-2	32.7 [831]	29.4 [745]
VIS-LS-SS-3030-4	32.7 [831]	29.4 [745]
VIS-LS-SS-3036-2	32.7 [831]	35.4 [900]
VIS-LS-SS-3036-4	32.7 [831]	35.4 [900]
VIS-LS-SS-3048-2	32.7 [831]	47.4 [1205]
VIS-LS-SS-3048-4	32.7 [831]	47.4 [1205]
VIS-LS-SS-3636-2	38.7 [983]	35.4 [900]
VIS-LS-SS-3636-4	38.7 [983]	35.4 [900]
VIS-LS-SS-3648-2	38.7 [983]	47.4 [1205]
VIS-LS-SS-3648-4	38.7 [983]	47.4 [1205]
VIS-LS-SS-3660-2	38.7 [983]	59.4 [1510]
VIS-LS-SS-3660-4	38.7 [983]	59.4 [1510]
VIS-LS-SS-3672-2	38.7 [983]	71.4 [1815]
VIS-LS-SS-3672-4	38.7 [983]	71.4 [1815]

NOTES:.

1. DIMS IN [ ] ARE IN mm.

