



VIS SYSTEM	DIM A	DIM B	DIM C in.	DIM D in.
VIS2424-IG2-125N	24.0 in	24.0 in	26.8	26.8
VIS2436-IG2-125N	24.0 in	36.0 in	26.8	38.8
VIS3030-IG2-125N	30.0 in	30.0 in	32.8	32.8
VIS3036-IG2-125N	30.0 in	36.0 in	32.8	38.8
VIS3048-IG2-125N	30.0 in	48.0 in	32.8	50.8
M-VIS2424-IG2-125N	600 mm	600 mm	26.8	26.8
M-VIS2436-IG2-125N	600 mm	900 mm	26.8	38.8
M-VIS3030-IG2-125N	750 mm	750 mm	32.8	32.8
M-VIS3036-IG2-125N	750 mm	900 mm	32.8	38.8
M-VIS3048-IG2-125N	750 mm	1200 mm	32.8	50.8

