



Model	DIM A THREAD	DIM B THICKNESS	DIM C CLEAR APERTURE	DIM D THRU HOLE
MLH-0.5-RR	0.546-32	0.093 (2.4)	0.40 (10.1)	0.031 (0.79)
LPLH-75-RR	0.786-32	0.093 (2.4)	0.625 (15.9)	0.031 (0.79)
LP-05-RR	0.875-20	0.093 (2.4)	0.643 (16.3)	0.031 (0.79)
A-1.25-1RR	1.063-20	0.127 (3.2)	0.76 (19.2)	0.062 (1.6)
LP-1-RR	1.438-20	0.127 (3.2)	1.06 (26.9)	0.062 (1.6)
LP-2-RR	1.563-20	0.127 (3.2)	1.18 (30.0)	0.062 (1.6)
LH2-T-RR	2.063-20	0.127 (3.2)	1.69 (42.7)	0.062 (1.6)