



RETAINING RING DIMENSIONS [ in (mm) ]					
MODEL	DIM A (THREAD)	DIM B (THICKNESS)	DIM C (CLEAR APERTURE)	DIM D (SLOT WIDTH)	DIM E (SLOT DEPTH)
LT05-RR	0.535-40	0.07 (1.8)	0.43 (10.9)	0.04 (1.0)	0.03 (0.76)
LT075-RR	M19.5 X 0.5	0.08 (2.0)	0.66 (16.8)	0.04 (1.0)	0.03 (0.76)
LT20M-RR	M20.5 X 0.5	0.08 (2.0)	0.695 (17.7)	0.04 (1.0)	0.03 (0.76)
LT10-RR	1.035-40	0.08 (2.0)	0.90 (22.9)	0.04 (1.0)	0.03 (0.76)
LT30M-RR	M30.5 X 0.5	0.08 (2.0)	1.10 (27.9)	0.04 (1.0)	0.03 (0.76)
LT15-RR	1.535-40	0.1 (2.5)	1.40 (35.6)	0.05 (1.3)	0.04 (1.0)
LT20-RR	2.035-40	0.1 (2.5)	1.87 (47.5)	0.05 (1.3)	0.04 (1.0)
LT30-RR	3.035-40	0.1 (2.5)	2.80 (71.1)	0.05 (1.3)	0.04 (1.0)