



Model (Metric)	Thread		Dimensions [in. (mm)]		
	A	B	C	D	
401	1/4-20 (M6)	1.0 (25.0)	4.0 (100.0)	0.75 (19.8)	
406	1/4-20 (M6)	1.0 (25.0)	4.0 (100.0)	0.75 (19.8)	