



Model	Thread	Diameter [in. (mm)]				Dimensions			Diameter [in. (mm)]	
	A	B	C	D	E	F	G	H	J	K
LH1-0.25R	1.063-20	0.26 (6.6)	0.19 (4.8)	1.88 (47.8)	1.49 (37.8)	0.56 (14.2)	0.38 (9.7)	0.03 (0.8)	0.10 (2.5)	0.19 (4.8)
LH1-0.5R	1.063-20	0.52 (13.2)	0.44 (11.2)	1.88 (47.8)	1.49 (37.8)	0.56 (14.2)	0.38 (9.7)	0.03 (0.8)	0.10 (2.5)	0.44 (11.2)
LH1-1R	1.063-20	1.01 (25.7)	0.94 (23.9)	1.88 (47.8)	1.49 (37.8)	0.56 (14.2)	0.38 (9.7)	0.06 (1.6)	0.06 (1.6)	0.76 (19.3)
LH2-1.5R	2.063-20	1.52 (38.6)	1.38 (35.1)	2.66 (67.6)	2.24 (56.9)	0.68 (17.3)	0.50 (12.7)	0.10 (2.5)	0.25 (6.4)	1.38 (35.1)
LH2-2R	2.063-20	2.01 (51.1)	1.88 (47.8)	2.66 (67.6)	2.24 (56.9)	0.68 (17.3)	0.50 (12.7)	0.10 (2.5)	0.10 (2.5)	1.69 (42.9)

