



Model	Dimensions [in. (mm)]		Thread
	A	B	
AJS127-02H	1.23 (31.2)	0.25 (6.4)	1/4-127
AJS127-0.5H	1.43 (36.3)	0.50 (12.7)	1/4-127
AJS100-02H	1.23 (31.2)	0.25 (6.4)	1/4-100
AJS100-02H-V6	1.23 (31.2)	0.25 (6.4)	1/4-100
AJS100-0.5H	1.43 (36.3)	0.50 (12.7)	1/4-100
AJS100-0.5H-V6	1.43 (36.3)	0.50 (12.7)	1/4-100
AJS100-1H	2.10 (53.3)	1.00 (25.4)	1/4-100
AJS100-1H-V6	2.10 (53.3)	1.00 (25.4)	1/4-100