



Model (Metric)	Thread		Dimensions [in. (mm)]								
	A	B	C	ϕD	E	F	ϕG	H	J	K	ϕL
UTR46A	8-32 (M4)		1.000 (25.0)	0.291 (7.4)	1.00 (25.4)	2.98 (75.8)	1.81 (46)	1.97 (50)	3.50 (89)	1.30 (33)	0.71 (18)
UTR46SA	8-32 (M4)		1.000 (25.0)	0.291 (7.4)	1.00 (25.4)	2.98 (75.8)	1.81 (46)	1.97 (50)	3.50 (89)	0.91 (23)	0.87 (22)
UTR80A	8-32 (M4)	1/4-20 (M6)	2.000 (50.0)	0.295 (7.5)	1.98 (50.4)	3.98 (101.1)	3.11 (79)	3.15 (80)	4.72 (120)	1.81 (46)	1.063-20 (M30 x 0.75)
UTR80SA	8-32 (M4)		2.000 (50.0)	0.295 (7.5)	1.98 (50.4)	3.98 (101.1)	3.11 (79)	3.15 (80)	4.72 (120)	0.91 (23)	1.97 (50)