



Model	Dimensions [in. (mm)]						Clamp Mounting	
	A	B1	C Nominal <sup>(1)</sup>	D	E	F	I	J
U50-P	1.00 (25.4)	0.82 (20.8)	0.70 (17.8)	0.375 (9.5)	0.50 (12.7)	-	1/4-20 (M6)	-
U100-P	2.00 (50.8)	1.79 (45.5)	1.14 (29.0)	0.63 (15.9)	1.00 (25.4)	1.79 (45.5)	1/4-20 (M6)	8-32 (M4)
U200-P	2.75 (69.9)	1.95 (49.5)	1.31 (33.3)	0.63 (15.9)	1.38 (35.1)	2.17 (55.1)	1/4-20 (M6)	8-32 (M4)

1) Dimension based on AJS100-0.5K-NL adjustment screw. 2) U50-P, U100-P and U200-P mounts have 8-32 (M4) counterbored clearance holes for post mounting. U50-PS has only two actuators.