



Model	A=B=C=
05BR08	0.5 in. (12.7 mm)
05SR20	0.5 in. (12.7 mm)
10BR08	1.0 in. (25.4 mm)
10SR20	1.0 in. (25.4 mm)
BRP-10	10.0 mm
BRP-12.7	12.7 mm
BRP-15	15.0 mm
BRP-20	20.0 mm
BRP-25.4	25.4 mm
BRP-30	30.0 mm
BRP-40	40.0 mm
BRP-5	5.0 mm
BRP-50.8	50.8 mm