



| Model | Dimensions | | | | | | Diameter [in. (mm)] | | | |
|-------|-------------|-------------|-------------|--------------|-------------|--------------|---------------------|-------------|--|--|
| | A | B | C Min | C Max | D Min | D Max | E Min | E Max | | |
| AC-1A | 2.48 (63.0) | 1.93 (49.0) | 2.62 (66.5) | 3.46 (87.9) | 2.52 (64.0) | 3.98 (101.1) | 0.2 (5) | 1.82 (46.2) | | |
| AC-2A | 2.96 (75.2) | 2.33 (59.2) | 3.12 (79.2) | 3.94 (100.1) | 2.95 (74.9) | 4.40 (111.8) | 0.70 (17.8) | 2.25 (57.1) | | |