



Model	A	B	C	D
M-SA2-FT-50	38.1 mm	25.4 mm	M6	13.1 mm
M-SA2-FT-70	38.1 mm	25.4 mm	M6	13.1 mm
SA2-FT-50	1.5 in.	1 in.	1/4-20	0.35 in.
SA2-FT-70	1.5 in.	1 in.	1/4-20	0.35 in.