



Model	Dimensions [in. (mm)]						D	E
	A	B Min	B Max	C Min	C Max			
SM-13 & SM-13LH	2.36 (59.9)	1.18 (30)	1.69 (43)	0.05 (1.3)	0.56 (14.2)	0.157 (4.0)	0.51 (12.9)	
SM-25	3.83 (97.3)	1.98 (50.2)	2.96 (75.2)	0.26 (6.6)	1.23 (31.2)	0.276 (7.0)	0.625 (15.9)	
SM-50	5.70 (144.8)	2.95 (74.9)	4.92 (125)	0.157 (4.0)	2.13 (54.1)	0.276 (7.0)	0.625 (15.9)	