



Counterbore Threaded Adaptor Nuts Model	Dimensions	Thread	Dimensions
	[in. (mm)] A	B	[in. (mm)] C
CN-E8-6	0.27 (6.9)	8-32	0.16 (4.0)
CN-E8T-6	0.38 (9.5)	8-32	0.25 (6.4)
CN-Q20-6	0.38 (9.5)	1/4-20	0.25 (6.4)
CN-M4-6	0.27 (6.9)	M4	0.16 (4.0)
CN-M4T-6	0.38 (9.5)	M4	0.25 (6.4)
CN-M6-6	0.38 (9.5)	M6	0.25 (6.4)