



Model	Dimensions [in. (mm)]		Thread
	A	B	
AJS8-100-02H	0.88 (22.4)	0.25 (6.4)	8-100
AJS8-100-0.5H	1.16 (29.5)	0.50 (12.7)	8-100
AJS8-100-0.5H-V6	1.16 (29.5)	0.50 (12.7)	8-100