



Model	A
9311*	0.96-in (24.4 mm)
9311-K	0.86-in (21.8 mm)
9312*	1.14-in (28.9 mm)
9312-K	0.99-in (25.1 mm)
9313*	1.33-in (33.7 mm)
9313-K	1.36-in (34.5 mm)
9314*	1.83-in (46.5 mm)
9314-K	1.86-in (47.2 mm)
9316*	2.83-in (71.9 mm)
9316-K	2.86-in (72.6 mm)
9317*	1.58-in (40.1 mm)
9317-K	1.61-in (40.9 mm)
9318*	2.18-in (55.4 mm)
9318-K	2.21-in (56.1 mm)
9376*	1.12-in (28.4 mm)
9376-K	1.15-in (29.2 mm)
9377*	1.24-in (31.5 mm)
9377-K	1.27-in (32.3 mm)
9378*	1.49-in (37.8 mm)
9378-K	1.52-in (38.6 mm)
9379*	1.74-in (44.2 mm)
9379-K	1.77-in (44.9 mm)

* Knob Not Shown