



Model	A
9341-K	0.45 in. (11.4 mm)
9341NF	0.43 in. (10.9 mm)
9342	0.56 in. (14.0 mm)
9342-K	0.57 in. (14.5 mm)
9343	1.10 in. (27.9 mm)
9343-K	1.12 in. (28.4 mm)
9344	0.86 in. (21.8 mm)
9344-K	0.88 in. (22.4 mm)
9345	0.73 in. (18.5 mm)
9345-K	0.75 in. (19.1 mm)
9346	1.36 in. (34.5 mm)
9346-K	1.38 in. (35.1 mm)
9347	1.49 in. (37.8 mm)
9347-K	1.51 in. (38.4 mm)
9371	0.72 in. (18.3 mm)
9371-K	0.74 in. (18.8 mm)
9372	0.79 in. (20.1 mm)
9372-K	0.81 in. (20.6 mm)
9373	0.92 in. (23.4 mm)
9373-K	0.94 in. (23.9 mm)
9374	1.22 in. (31.0 mm)
9374-K	1.24 in. (31.5 mm)
9375	1.34 in. (34.0 mm)
9375-K	1.36 in. (34.5 mm)